

Technical Specifications:

1. DirectlyR, ISO, CE, PP, PP / PE, SMS, SMMS, Tyvek

2. ISO, CE, PP, PP / PE, SMS, SMMS, Tyvek

3 Capacity: 10,000pcs / 1 * 40HQ

4 OEM

5

Application:

- 1.
2.
3.
4.
5.

Application:

- 1.
2.
3. Widely dustless

Coverall:

- B:
C:
D:
E:

Technical Specifications:

Material

Material

Coverall

Material

□□□□□□□□ 15 □□□□□□□□□□□□□□ 20feet