

XX

XXXXXXXXXX XXX XXXXXXXXXXXXXXXXXXXXXXX

XX

XXXXXXXXXX

XX/XX

XXXXXXXXXX XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX

XXXX	XXXXSMS
XXXX	XXXXX2XXXXXXXXXXXXXXXXXXXXXXXXXXXX
XXXXXX	78 * 11CMXXXXOEM
XXXXXX	16-40g /m <sup>2</sup>
XX	XXXXXXXXXXXXXXXXXXXXXXXXXXXX
MOQ	200000
XXXXXXXXXXXX	XXXXXXXXXXXXXXXXXXXXXXXXXXXX
XX	1XX/XXXX1000XX/ ctnXXXXXXXXXXXX
XX	7XX30XX
XXXXXXXXXXXX	XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX

XXXXXXXXXX XXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXXX

