

1. PP
2. 2060/
- 3./
- 4./
- 5.
6. 10,000/1 *40HQ1015
7. OEM24
8. CEFDAISO 9001

□ □ □ □ □ □ □ □ □

1.
 2.
 3.

□ □ □ □ □ □ □ □ □ □ □ □

[illegible]

□□□	□□□□□□□
□□□	PP□□
□□	20-50gsm
□□□□□	□□□□□□□
	□□□□□□□□□□;
	□□□/□□□□/□□□□/□□□□□□□□□□
	/□□□□□□□
	□□□□□□□□□□□□□□□□

MOQ	workshop
	,
	5000
	510 / 50100 / CTN
	80
	T / T L / C D / A D / P

0000000000	OEM000000000000/0000
000	CE0ISO13485
00	C00apacity010,0000/00 1 * 40HQ01001500000000000000

□ □ □ □ □ □ □ □ □ □ □ □

