



| | |
|----------|---------------------------------|
| □□□ | 3D □□ □□ KF94 □□□ □□□ |
| BFE, PFE | bfe≥95% |
| □□ | PP+ □□ BLOWN+ MELT BLOWN+ PP |
| □□ | □□ □□ □□ □□, □□ □□□ □□ |
| □□□ | □ □□ |
| □□ | 50g+25g+25g+30g □□ □□□ □□ |
| □□ | □□□ □□ 20x8cm, □□□ □□□□ □□ |
| □□ | 50pcs/bag, 40bag/□□, 2000pcs/□□ |
| □□ □□ | 7-15 □ |
| □□ □□ | T/T, L/C, X-Transfer, PayPal, □ |
| □□□ | OEM, □□□ □□, □□ □□ □□ |
| □□□ □□ | GB2626-2019 |

□□ □□□ □□□ □□ □ □ □□□□. □□□ □□□□□□.

✔ With high moisturizing transferability technique, it absorbs moisture quickly, boasting a fresh fit even if worn for a long time, and prevents misting even when wearing glasses.



- * 100% Cotton 4 layers
- * 3D pleated 3 layers 3D pleated 3 layers 3D pleated 3 layers
- * 100% Cotton 3 layers 3D pleated 3 layers
- * 100% Cotton
- * 100% Cotton 3 layers 3D pleated 3 layers

100% Cotton 3 layers 3D pleated 3 layers, 100% Cotton 3 layers









