

□□ □□□□□□ □□□ □□□ □□□□□ □□

□□ □□ □□ □□□ □□□ □□□ □□ □□ □□ □□□ □□□□□□.

- □□□□□ □□ □□□ □□□□□.

- □□□ □□□ □□ □□□□ □□□□□.

- □□□□ □□ □ □□□

□□□□□□ □□□ □□□□ **17*23.5cm** □□ **80g**

□□ □□	□□□□
□□□□	□□ □, □□□ □□
□□ □□□	17*23.5cm
□□□ □ □□	50-80g□, □□□ □□□ □□□□ □ □□□□
□□	□□□□ □□
MOQ:	1 00 , 0 0 0□
□□ □□□	□□□ □□□□□ □ □ □□□□
□□	1 □/b □□ , 600 PC s/ctn □□ □□□ □□ □□□□
□□ □□	7~30□
□□	□□ □□□,□□□□□ □□□

□□ □□□□□ □□□ □□







