

□□□ □□ □□ □□ □□ □□ □□ :

□□ □□:	□□□□ □□ □□ □□, PP + PE □□□□ □□ □□
□□□□:	□□ □□□□ (PP □ □)+ PE □□
□□:	PP25-35GSM + PE □□
□□□:	□□ □□, □□□ □□ PE □□,
□□	□□ □□□
□□:	38x15cm, 40x15cm, 41x17cm ... ..
□□:	100PCS / □□, 2000PCS / CTN
□□ □□□□:	□□□□electronics □□, □□ □□, □□ □□ □ □□ □□□□□ □□ □□□ □□□□ □□□□.
MOQ :	(10)0000 □
□□ □□:	T / T, □□□, □□□ □□□, L / C, D / A, D / P, □□□□,
□□□:	CE / ISO13485

□□ □□:

1. D□□ □□ □□ □□ □□ □□ □□□□□□ PP □□□□ □□□□ □□□ □□ □□ □□□□ □□ □□□□ □□□□□ □□□ □□ PE □□, □□ . □□ □□□ □□□ 2 □□□ □□ □□□ □□□□□□□□.□□□□ □□□□□ □□ □□□□.

□ □□ □□□ □□ □□ □□ □□ □□ :



