000 000 000 00 :

|| || : 30-65gsm.

pplication :

- $1. \square \square$, $\square \square$, $\square \square$, laboratorial, $\square \square \square \square$
- $2. \ \, \Box\Box\Box\ \, \Box\Box\Box\ \, \Box\Box\Box\Box\ \, \Box\Box\Box\Box, \ \, \Box\Box, \ \, \Box\Box, \ \, \Box\Box, \ \, \Box\Box\ \, \Box\Box\Box\Box\ \, \Box\Box\Box.$

 $\square \square : 5 \ \square \ / \ \square \square, \ 50 \ \square \ / \ AG \ \square \square \ 1 \ \square \ / \ \square \square, \ 50 \ \square \ / \ CTN$

L (1185 ≸)

000 000 000 00:

	000 000 00
	PP [] []
	o / 0000 oo / 00000 /, 000 000000 oo 000 o 0000.
	S-6XL
	5PCS / [][], 10 [][] / CTN
00 000	00 00 00 00 000 000 00000 0 000
MOQ	(5)000 [
	3 0 000 0000 000 00 0 0 0 0000
	T / T, [][], [][] [][], L / C, D / A, D / P, [][][],
	apacity : 10,000 / _, 1 * 40HQ 10-15
FOB □□	

000 000 000 00 **:**



