

1. 2. 3. 4. 5. 6.

1. 2. 3. 4. 5. 6.

1. 2. 3. 4. 5. 6.
2. 3. 4. 5. 6.
3. 4. 5. 6.
4. 5. 6.
5. 6.
6. 7. 8. 9. 10. 11. 12. 13. 14. 15. 16. 17. 18. 19. 20. 21. 22. 23. 24. 25. 26. 27. 28. 29. 30. 31. 32. 33. 34. 35. 36. 37. 38. 39. 40. 41. 42. 43. 44. 45. 46. 47. 48. 49. 50. 51. 52. 53. 54. 55. 56. 57. 58. 59. 60. 61. 62. 63. 64. 65. 66. 67. 68. 69. 70. 71. 72. 73. 74. 75. 76. 77. 78. 79. 80. 81. 82. 83. 84. 85. 86. 87. 88. 89. 90. 91. 92. 93. 94. 95. 96. 97. 98. 99. 100.


1. 2. 3. 4. 5. 6.

1. 2. 3. 4. 5. 6.
2. 3. 4. 5. 6.
3. 4. 5. 6.
4. 5. 6.


1. 2. 3. 4. 5. 6.

| | |
|-------------------|-------------------|
| 1. 2. 3. 4. 5. 6. | OH-4000. |
| 1. 2. 3. 4. 5. 6. | 1. 2. 3. 4. 5. 6. |
| 1. 2. 3. 4. 5. 6. | 1. 2. 3. 4. 5. 6. |
| 1. 2. 3. 4. 5. 6. | 1. 2. 3. 4. 5. 6. |
| 1. 2. 3. 4. 5. 6. | 1. 2. 3. 4. 5. 6. |
| 1. 2. 3. 4. 5. 6. | 1. 2. 3. 4. 5. 6. |
| 1. 2. 3. 4. 5. 6. | 1. 2. 3. 4. 5. 6. |
| 1. 2. 3. 4. 5. 6. | 1. 2. 3. 4. 5. 6. |


1. 2. 3. 4. 5. 6.
2. 3. 4. 5. 6.
3. 4. 5. 6.
4. 5. 6.
5. 6.
- 6.




single collar,
open wrist




single collar,
elastic wrist



knit collar,
knit wrist
3 pockets



single collar,
open wrists
3 pockets



single collar,
elastic wrists
3 pockets

□□□ □□□□ □□ :

1. □□□ □□ □□□□ PC / □□, 50pcs / ctn
2. □ □□ (□□ □□)
3. □□ □□ : 30 * 28 * 38cm, □□□ □□□ 0.0475cbm
4. 1x20GP□ □□□□ 861ctns□□□□ □ □ □□□□. □□□ 43050pcs□□□□.
- 1x40hq□ □□□□ 2114ctns□□□□ □ □ □□□ □□□ 105700pcs□□□□.

□□□□ □□

1. □□□ □□□□ □□ □□ □□□□□? □□□□ □□□ □□ □□□□□?

□, □□□ □□ □□ □□, □□□ □□□ 2003 □□ □□□□□□□.

2. □□□ □□ □□□□ □□□□□?

□□ □ □□□ 180 □ ~ 2 □□ □□ □□ □□□□ □□□□.

3. □□□ □□□ □□ □□ □□□□□?

□□□ □□□ □ □□□□ □□ □□ □□ □ 10-8 □ □□□ □□ 10 □□ □□ □□ □□□□□ 10 □□ □□ QC□ □□□□ □ 380-400 □□ □ □□□, 10 □□ □□ QC.

4. □□□ □□ □□□ □□ □□□ □□□□ □□ □ □ □□□□?

□□, □□□ 90 %, □□□ 10 %.

5. □□□ □□□□ □□ □□□□ □□ □□□□□?

□□, □□□□, □□□□□□, □□□□□, □□□□, □□, □□, □□□ □□□□□, □□, □□□□, □□, □□□□, □□, □□, □□ □□.

6. □□□ □□□□ □□□ □□□ □□ □□□ □□ □ □ □□□□?

□□ □□□ □□□ □□ □□□ □□ □□□, □□, coveralls, □□ □ □□, □□□□, □□ □□, □ □□□□, □□ □□□, □□ □ □□, □□ □□□, □□□□ □□ □□ □□ □□□□□.

[illegible]

2 000 PP, SMS, PP / PE 0000 00 00. 00 00 000000 2 00 000000 0000 5 00 0 00 0 5 00 00 00 00 00. 10 00 0000 0000 00.

8. □□□ □□ □□□ □□□ □□ □□□ □□□□□?

□□ □□□ □□ : 1000,000 □□ / □. overall, □□ □ □□, □□□ □□, □□ □□ □□ : 10,000 □□ / □. □ □□ : 200,000 □□ / □. □
1 * 40HQ□ 7-10 □ □□□ □□ □ □ □□□.

9. 如何符合 ISO, EN 及 CE 認證的鋼筋 鋼絲 鋼索 鋼管 鋼板?

□, □□□ CE, ISO13485, FDA, REACH, SGS □ Nelson □□□□ □□□□ □□□□.

10. ພຶ້ນ ແມ່ນ ພື້ນ ທີ່ ມີ ສິ່ງ ຂອງ? ພື້ນ ແມ່ນ ພື້ນ ທີ່ ມີ ສິ່ງ ຂອງ?

□, □□□ □□□ 3-7 □ □□□ □□□ □□ □ □ □□□□.

11. □□□ □□□ □□□□□ □□ □ □ □□□□?

□, □□ □□ □□ □□ □ □ □□ □□ □□□□ □□□□ □□ □ □ □□□□.

12. 何種 樹木 樹皮 剥離 後 剥離 面 腐敗 腐敗 腐敗?

□ 3-5 □.

13. □□□□ □□ □□□ □□□□□?

1. 30 % T / T 70 % L / C .

14. □ □□ MOQ □ □□□□?

□□ □□□ / □ / □ □□ / □ □□□ □ MOQ : 50,000 □□. □ □ □□ MOQ : 5000 □□.

15. □□ □□ □□ □□ □□ □□□□?

[illegible]





<https://www.china-disposable.com/products/yellow-collar-disposable-gown.html#.ypqm-gzauk>.