

□□□ □□ □□

□□□ □□ □□□ □□□ □□ □□ □□. □□□□ □□ □□□□□ □□ □□ □ □□ □□. □□ □□ □ □□□ □□□□ □□□□□. □ □□□ □□□ □□□ □ □□ □□□□ □□□ □□□□ □□□ □□□□□. , □□, □□□, □□, □□□□ □ □□□□ □□.

□□□ □□ □□□ □□

□□□ □□	PP, PP / PE, SMS, SMMS.
□□□	□□□, □□□□ □, □□ □, □
□□	80x190 + 20cm, 90x200 + 20cm, 160x190 + 20cm, 160x200 + 20cm, 180x200 + 20cm
□□	□□, □□, □□, □□, □□□ □
□□	10pcs / □□, 10 □□ / CTN □□ 5 PCS / BAG, 50 PC / BAG.
□□ □□□	□□□□□□ □ □ □□□□ □□□
MOQ	5000pcs.
□□	□□□ □□□ □□ □□□ □□ □ □ □□□□ 3 □ □□□ □□□□□□
□□ □□	□□ : 10,000pcs / □, 1 * 40HQ□ 10-15 □ □□□ □□ □ □ □□□□.
FOB □□	□□ / □□□ / □□ / □□□

□□











