

## Product details

### The feature of the dust face mask

- 1) Use ultrasonic welding technology ;
- 2) Ear loop: elastic ear loop
- 3) We can add sponge to mask comfortable wearing .
- 4) Very low resistance for breathing, free from foreign smell, without any stimulating feeling
- 5) Colors could be white (normal style ), and gray (carbon active style) .
- 6) Material is environmental friendly, latex free .

### Our industrial dust face mask can reach following quality standard

N95, EN 149:2001 (FFP1,FFP2,FFP3)

### Packaging of dust mask with exhalation valve

20 pcs/box,400 pcs/ctn, or as your requirement

## Product display



## The regular shipment way



## FAQ

Q: 1.Are you a manufacturer or a trading company, and when was your company established?

A: Yes, we are directly manufacturer, our factory was established in 2003, we have our own exported rights company in 2013.

Q: 2.What is the annual turnover for your company?

A: Normally it is around USD18 million-20 million, it is still in the growing.

Q:3. What is the number of employees at your company?

A: Our factory is about 380-400 skilled workers, 10 professional QC for quality checking during each process and 10 professional int'l sales with 3-8 years experience in int'l trade department.

Q:4. What is the percentage of your products distribution for local, and export?

A: At present, 90% for export,10% for local.