

Product details

Applications of disposable dust mask

- 1) Building construction, hospital.
- 2) Fiber exposure and fiberglass products manufacturing
- 3) Pharmaceutical manufacturing
- 4) Painting and spraying workshop
- 5) Electronic assembly and insulation laying
- 6) Mining, wood, and metal processing
- 7) Motor vehicle and ship building
- 8) Agriculture and veterinary services
- 9) Asbestos removal, stripping, and clear-up or handling

We have following types of dust mask

- 1) Cup shape and folded flat
- 2) With breathing valve or without breathing valve
- 3) 1 layer , 3 layers, 4 layers, 5 layers


Packaging of paper dust mask

Type	Packaging details	Ctn size
Cup shape (without valve)	20pcs/box, 20boxes/carton	62×27×42 cm
Cup shape (with valve)	10pcs/box, 30boxes/carton	65×29×42 cm
Folded type (without valve)	20pcs/box, 20boxes/carton	67×29×33 cm
Folded type (with valve)	10pcs/box, 30boxes/carton	67×29×35 cm

Product display



Our business process



The regular shipment way

