

Product details

Applications of disposable dust mask

- 1) Building construction, hospital.
- 2) Fiber exposure and fiberglass products manufacturing
- 3) Pharmaceutical manufacturing
- 4) Painting and spraying workshop
- 5) Electronic assembly and insulation laying
- 6) Mining, wood, and metal processing
- 7) Motor vehicle and ship building
- 8) Agriculture and veterinary services
- 9) Asbestos removal, stripping, and clear-up or handling

We have following types of dust mask

- 1) Cup shape and folded flat
- 2) With breathing valve or without breathing valve
- 3) 1 layer , 3 layers, 4 layers, 5 layers


Packaging of paper dust mask

| Type | Packaging details | Ctn size |
|-----------------------------|---------------------------|-------------|
| Cup shape (without valve) | 20pcs/box, 20boxes/carton | 62×27×42 cm |
| Cup shape (with valve) | 10pcs/box, 30boxes/carton | 65×29×42 cm |
| Folded type (without valve) | 20pcs/box, 20boxes/carton | 67×29×33 cm |
| Folded type (with valve) | 10pcs/box, 30boxes/carton | 67×29×35 cm |

Product display



Our business process



The regular shipment way

