

Product details

Application of anti-static shoe cover

Mainly used in dust-free workshop, electronic manufactures factory and so on.

It's good protective,lightweight,latex free, and anti-static.

Details of disposable anti-static shoe cover

1. PP material,with plastic conductive strip
2. The shoe cover is machine made, the plastic conductive strip is hand-made.
3. Available color: white, blue,green, etc
4. We are the OEM manufacturer, can produce as your requirements or samples.

Our advantage

1. Direct manufacturer,factory price ;
2. 1*40 HO container can be finished in 15 days;
2. CE ISO13485 FDA approved,stable quality;
3. Service in 24 hours,sample can be finished in 2 days,sample free.

Specifications of non woven anti-static shoe cover

Material	PP
Fabric weight	25g up
Style	Machine made elastic + hand made conductive strip
Size	15×40cm,or as your requirement
Color	white,green,blue,etc.
Packing	10pcs/roll, 100pcs/bag,2000pcs/ctn,or as your demand
Packing design	all inner bag and carton printing can be as your design
Applications	dust-free workshop, electronic manufactures factory and so on.

Product display



orient Honest
MEDICAL INTERNATIONAL

