

## **Disposable anti-fog face mask , double nose clip face mask , nonwoven face mask with 2 nose bar**

### **Our disposable anti-fog face mask can achieve following quality standard**

- 1) Conform to EN14683: 2005
- 2) Bacterial filtration efficiency (BFE%) > 99%.
- 3) TYPE IIR standard, resistance to penetration by synthetic blood-120mmHg.

### **Packaging of double nose clip face mask**

Normally, 50 pcs/box,40 boxes/ctn

Box size: 18\*10\*7cm; Carton size: 52\*38\*30cm

1\*40 HQ can hold 2,300,000 Pcs (1150 Ctns)

Or as your requirements.

### **Description of face mask with 2 nose bar**

- 1) The common sizes what we produced is 175\*95mm, one size fit all;
- 2) It is made of top-grade non-woven fabrics;
- 3) With elastic or tie on earloop ;
- 4) It's designed for the customers who wear glasses, to protect the breathing air blur the glasses;
- 5) With double nose bar, more comfortable ;
- 6) can make any color as your like.

### **The trade terms of disposable anti-fog face mask**

MOQ	100,000 pcs
Price	Negotiable
Payment terms	T/T, L/C, D/A, D/P, Western Union, ESCROW,Paypal
Supply ability	1,000,000 pcs/day,1*40 HQ container can be finished in 15 days
Delivery time	Normally 30 days after confirmed the order
Sample	Sample is free, can be prepared well in 2 days

### **Picture of double nose clip face mask**



