

The property of level 3 ultrasonic seam disposable isolation gown

Waterproof, quiet highly fluid repellent for use in even the most challenging procedures

Ergonomically designed for greater ease of movement

Available in Standard, added protection against strike through

High Performance

The Specification of level 3 ultrasonic seam disposable isolation gown

| | |
|-----------------|---|
| Fabric Material | PP+PE, PP coated PE film |
| Style | With Velcro on collar, ties on waist |
| Dimensions size | 120*140cm, 130*150cm |
| Color | White, blue, yellow, or as your request |
| Certificate | CE, ISO13485, FDA |
| MOQ: | 100,000pcs |
| Packing design | can be as your design |
| Packing | 10pcs/bag, 1000pcs/ctn, or as your requirement |
| Capability | 50,000pcs per day |
| Delivery time | 5-15 days |
| Applications | hospital, laboratory, clinic, food industry, dust-free workshop |

The picture of level 3 ultrasonic seam disposable isolation gown



