

## Product details

### The design details of disposable protective coverall

- 1) Material: Microporous film SF, breathable and waterproof
- 2) With hoods, without boots
- 3) 1 way zipper in front
- 4) Elastic cuff and ankle
- 5) We can also produce as your actual requirements

### Packaging of disposable protective coverall

Normally, 1Pcs/bag, 50Pcs/Ctn

Ctn size : 50\*28\*59cm

1\*40 HQ container can hold : 40000 Pcs (800 Ctn )

### Specifications of disposable protective coverall

Material	Microporous film
Grammage	55g, or as your request from 45g--65g
Style	With hood, with elastic in waist, without boots
Size	XS-6XL
Color	White
Packing	1pcs/box, 50 bags/ctn, or as your requirement
Packing design	All inner bag and carton printing can be as your design
Applications	Dust-free workshop, hospital, laboratory, food industry, electronic manufactures and so on

### Indication of disposable protective coverall

- 1) The permeability of the coverall is strong, anti-static, acid and alkali corrosion resistance at the same time.
- 2) It's widely used in hospital, aseptic workshop, protective isolation environment, mining electronics factory, food factory, animal farm and so on.

## Product display



orient Honest  
MEDICAL INTERNATIONAL






orient Honest  
MEDICAL INTERNATIONAL



## Our business process



## The regular shipment way



## FAQ

**Q: 1. Are you a manufacturer or a trading company, and when was your company established?**

A: Yes, we are directly manufacturer, our factory was established in 2003, we have our own exported rights company in 2013.

**Q: 2. What is the annual turnover for your company?**

A: Normally it is around USD18 million-20 million, it is still in the growing.

**Q: 3. Do your company have any quality management system such as ISO, EN or CE certificate(s)?**

A: Yes, we have CE, ISO13485, FDA, REACH and NELSON report.

**Q: 4. Can I get the free samples for quality checking? How long time can I get it?**

A: Yes, our samples can be supplied free within 3-7 days.

